

Expertise Applied Answers Delivered

## PolySwitch® PTC Devices

**Overcurrent Protection Device** 

### PRODUCT: RUSBF160

DOCUMENT: SCD25247 REV LETTER: F REV DATE: JULY 26, 2016 PAGE NO.: 1 OF 2

# Specification Status: Released

## **Electrical Rating**

## Voltage: 16V<sub>DC</sub> MAX

Current: 40A MAX

#### Insulating Material:

Cured, Flame Retardant Epoxy Polymer meets UL 94 V-O Requirements

#### Lead Material:

24 AWG Tin Plated Copper Clad Steel

### Marking:

Manufacturer's Mark

X R160 and Part Identification

Lot Identification




	TABLE I. DIMENSIONS:												
	A		B		Ç		D		E				
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX			
mm:		8.9		15.2	4.3	5.8	7.6			3.0			
in*:		(0.35)		(0.60)	(0.17)	(0.23)	(0.30)			(0.12)			
	*Rounded off approximation												
TABLE II. PERFORMANCE RATINGS :													
	I HOLD		CUR	RENT	IN	INITIAL RESISTAN			ONE HOUR		TIME TO	TRIPPED-	
	RATED		RATINGS			VALUES			POST-TRIP		TRIP	STATE	
	CURRENT							RESISTANCE		@ 8A	POWER		
								STANDARD			DISSIPATI		
					011140			TRIP			ON		
	AMPERS			ERES		OHMS AT 20°C			OHMS AT 20°C		SECONDS	WATTS	
	AT 20°C HOLD		AT 20°C HOLD   TRIP		N AL						AT 20°C	AT 20°C	
_	1.60		1.60	3.20				0.061	 0.11		9	0.9	
							.05	0.001	0.11		9	0.9	
Agency Recognitions: UL, CSA, TUV Reference Documents: PS300													
Precedence: This specification takes precedence over documents referenced herein.													
Effectivity: Reference documents shall be the issue in effect on the date of invitation for bid.													
CAUTION: Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.													
Materials Information													
RO	ROHS Compliant ELV				Complia	nt	Pb-Free		e H		lalogen Free*		
Dir	ective 20					0/53/EC				]	HF		
Compliant Compliant													

\* Halogen Free refers to: Br≤900ppm, Cl≤900ppm,Br+Cl≤1500ppm.



# PolySwitch® PTC Devices

**Overcurrent Protection Device** 

PRODUCT: RUSBF160

DOCUMENT: SCD25247 REV LETTER: F REV DATE: JULY 26, 2016 PAGE NO.: 2 OF 2

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, military, aerospace, medical, lifesaving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.